


DUAL USB WALL CHARGER WITH COUNTDOWN TIMER

model no. 299-9909-6 | contact us: 1-866-827-4985

IMPORTANT: Please read this manual carefully before use and save it for reference.

INSTRUCTIONS:

1. Plug the timer into an easily-accessible AC outlet. The power LED indicator will be on, and USB1 and USB2 will have a constant 5 V output each. (Warning: Do not exceed 2400 mA in total.)
2. Press the Timer button to scroll through the countdown timer options. The timer can be set to 6 h, 4 h, 2 h, 1 h, or always on. When the timer reaches the set countdown time, the power to the USB outlets is turned off and the LED indicator turns off.
3. To turn the device on again, press the Timer button and repeat step 2.



SPECIFICATIONS:
125 V AC, 60 Hz, 0.3 A
USB output: 5 V DC
Max. 2 400 mA (each)
Max. 2 400 mA (total)
Class 2 Power Unit
CANICES-003(B)/NMB-3(B)

⚠ CAUTION:

1. For indoor use only.
2. The voltage and frequency of the connected appliance should be in accordance with the SPECIFICATION.

Caution

Warranty

This Noma product carries a one (1) year warranty against defects in workmanship and materials. Noma Canada agrees to replace the defective product free of charge within the stated warranty period, when returned by the original purchaser with proof of purchase. This product is not guaranteed against wear or breakage due to misuse and/or abuse.


CHARGEUR MURAL À PORT USB DOUBLE À MINUTERIE RÉGRESSIVE

N° de modèle : 299-9909-6 | Communiquez avec nous au 1 866 827-4985

IMPORTANT : Veuillez lire attentivement le présent guide avant l'utilisation et conservez-le aux fins de consultation ultérieure.

INSTRUCTIONS :

1. Branchez la minuterie à une prise CA facilement accessible. Le voyant lumineux à DEL s'allume et les ports USB1 et USB2 ont une sortie constante de 5 V chacun. (Avertissement : Ne dépassez pas 2 400 mA au total.)
2. Appuyez sur le bouton Minuterie pour faire défiler les options de la minuterie régressive. La minuterie peut être réglée sur 6 h, 4 h, 2 h, 1 h ou alimentation constante. Lorsque la minuterie atteint l'heure définie du compte à rebours, l'alimentation des sorties USB est coupée et le voyant lumineux à DEL s'éteint.
3. Pour remettre l'appareil en marche, appuyez sur le bouton Minuterie et répétez l'étape 2.



FICHE TECHNIQUE :
125 V CA, 60 Hz, 0,3 A
Sortie USB : 5 V CC
Max. 2 400 mA (chacun)
Max. 2 400 mA (total)
Bloc d'alimentation de classe 2
CANICES-003(B)/ NMB-3(B)

Attention

ATTENTION :

1. Conçu uniquement pour une utilisation à l'intérieur.
2. La tension et la fréquence de l'appareil branché doivent être conformes aux SPÉCIFICATIONS.

Ce produit Noma^{MD} comprend une garantie d'un (1) an contre les défauts de fabrication et de matériaux. Noma Canada consent à remplacer l'article défectueux sans frais lorsqu'il est retourné par l'acheteur original, accompagné de la preuve d'achat, au cours de la période de garantie convenue. Ce produit n'est pas garanti contre l'usure ou le bris causés par un usage abusif ou inapproprié.

FABRIQUÉ EN CHINE
Importé par Noma Canada
Toronto, Canada M4S 2B8

